



## Enclosure, vector, IP5x, 10 Modules, version Austria

## **Technical characteristics**

Connection	
Number of conduit inlets	6
Voltage	
Nominal voltage	400 - 400 V
nstallation, mounting	
Suitable for outdoor usage	No
Mounting on	Surface mounting
Electric current	
Rated current	63 A
Equipment	
Number of rails	1
Number of rows	1
Number of section in width	1
Nith lock	No
Has neutral terminal block	No
Has earthing terminal block	No
Has mounting plate	No
Capacity	
Number of modules	10
Functions	
With conduit inlets	Yes
Dimensions	
Height	210 mm
Width	237 mm
Depth	114 mm
Number of width units	10
Cover, door	
Number of cabinet doors	1
Number of locks	0
Door/cover is transparent	Yes
Materials	
Material	Polystyrene (PS)

RAL code	7035
Colour	Light grey
Ultraviolet-resistant	No
Safety	
Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP65
Locking type	Snap on lock, Without lock
Glow wire test	750 °C