



VE112R

Enclosure,vector,IP55,12Modules

Technical characteristics

Connection

Number of conduit inlets	12
--------------------------	----

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes
Has mounting plate	No

Capacity

Number of modules	12
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	302 mm
Width	310 mm
Depth	151 mm
Number of width units	12

Cover, door

Number of cabinet doors	1
Number of locks	0
Door/cover is transparent	Yes

Materials

Material	Plastic
----------	---------

RAL code	7035
Colour	Light grey
Ultraviolet-resistant	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK08
Ingress Protection (IP) class	IP65
Locking type	Snap on lock, Without lock
Glow wire test	750 °C