



VM10606

Consumer unit,Design30,dual row,6+6way,100A,switch disconnecter incomer

Technical characteristics

Architecture

| | |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

Main electrical features

| | |
|-----------|-------|
| Frequency | 50 Hz |
|-----------|-------|

Dimensions

| | |
|----------------------------|----------|
| Depth of installed product | 102.5 mm |
|----------------------------|----------|

| | |
|-----------------------------|--------|
| Height of installed product | 480 mm |
|-----------------------------|--------|

| | |
|----------------------------|--------|
| Width of installed product | 220 mm |
|----------------------------|--------|

Cover, door

| | |
|----------------------|-------------|
| Type of door closing | non keylock |
|----------------------|-------------|

| | |
|---------------|----|
| Interlockable | No |
|---------------|----|

Materials

| | |
|--------|------------|
| Colour | pure white |
|--------|------------|

| | |
|--------|-------|
| Colour | white |
|--------|-------|

| | |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
|------------|-----------------------|

| | |
|----------|-------|
| Material | Steel |
|----------|-------|

Equipment

| | |
|----------------|---|
| Number of rows | 2 |
|----------------|---|

| | |
|---------------------|-----|
| Can be accessorized | Yes |
|---------------------|-----|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|