



VM24AH



2 Way 40A 30mA Type A RCCB Incomer

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Dimensions

Depth of installed product	102 mm
Height of installed product	240 mm
Width of installed product	149 mm

Cover, door

Interlockable	No
---------------	----

Materials

Material	Steel
Type of surface treatment	powder-coated

Equipment

Number of rows	1
Can be accessorized	Yes

Standards

European directive WEEE	not concerned
-------------------------	---------------