



VM24AHK

## 2 Way 40A 30mA Type A RCCB Incomer with Knockouts

### Technical characteristics

#### Architecture

Fixing mode	surface-mounting
-------------	------------------

#### Dimensions

Depth of installed product	102 mm
Height of installed product	240 mm
Width of installed product	149 mm

#### Cover, door

Type of door closing	non keylock
Interlockable	No

#### Equipment

Number of rows	1
Can be accessorized	Yes

#### Standards

European directive WEEE	not concerned
-------------------------	---------------