



VM306AHK

6 Way 100A 30mA Type A RCCB Incomer with Knockouts

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Dimensions

Depth of installed product	102 mm
Height of installed product	240 mm
Width of installed product	221 mm

Cover, door

Interlockable	No
---------------	----

Materials

Material	Steel
----------	-------

Equipment

Number of rows	1
Can be accessorized	Yes

Standards

European directive WEEE	not concerned
-------------------------	---------------