



VM314AH

14 Way 100A 30mA Type A RCCB Incomer

Technical Characteristics

Fixing mode	surface-mounting
Rated current	100 A
Depth of installed product	102 mm
Height of installed product	240 mm
Width of installed product	364 mm
Number of modules	14
Type of door closing	non keylock
Interlockable	No
RAL colour number	9010
Material	Steel
Type of surface treatment	powder-coated
Number of rows	1
Can be accessorized	Yes
European directive WEEE	not concerned
Protection index IP	IP2XC