



VM610CUK

10 Way Hi Integrity Configurable 63A Switch 2*63A 30mA Type A RCCB with knockout

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Dimensions

Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	364 mm