



VM610CUKSPD

**Design 30 , 10 way Configureable HI 63A Sw 2\*63A 30mA RCCB Type A SPD**

**Technical Characteristics**

Fixing mode	surface-mounting
With remote signalling contact	No
Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	400 mm
RAL colour number	9010
Number of rows	1
Can be accessorized	Yes
Protection index IP	IP2XC