



VM61214CU

**Dual Row Hi Integrity 12+14 Way 63A Switch 2\*63A 30mA RCCB**

**Technical characteristics**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Dimensions**

Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	364 mm

**Cover, door**

Interlockable	No
---------------	----

**Materials**

Material	Steel
----------	-------

**Equipment**

Number of rows	2
Can be accessorized	Yes

**Standards**

European directive WEEE	concerned
-------------------------	-----------