



VM633HK

6 Way 3+3 63A Switch 2*63A 30mA Type A RCCB with knockouts

Technical Characteristics

Fixing mode	surface-mounting
Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	293 mm