



VM666HK

12 Way 6+6 63A Switch 2\*63A 30mA Type A RCCB with knockouts

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Dimensions

Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	400 mm

Cover, door

Interlockable	No
---------------	----

Equipment

Number of rows	1
Can be accessorized	Yes