



VM908CUKSPD

**Design 30 , 8 way Configureable HI 100A Sw 2\*100A 30mA RCCB Type A  
KO SPD**

---

**Technical Characteristics**

Fixing mode	surface-mounting
Rated current	100 A
Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	364 mm
Interlockable	No
Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Number of rows	1
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC