



VM910CUKSPD

Design 30 , 10 way Configurable HI 100A Sw 2*100A 30mA RCCB Type A SPD

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50 Hz

Dimensions

Depth of installed product 102.5 mm

Height of installed product 240 mm

Width of installed product 400 mm

Cover, door

Type of door closing non keylock

Interlockable No

Materials

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Equipment

Number of rows 1

Can be accessorized Yes

Standards

European directive WEEE concerned

Safety

Protection index IP IP2XC