



VM910CUKSPD

Design 30 , 10 way Configureable HI 100A Sw 2*100A 30mA RCCB Type A SPD

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Dimensions

Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	400 mm

Cover, door

Type of door closing	non keylock
Interlockable	No

Materials

Colour	pure white
Colour	white

Equipment

Number of rows	1
Can be accessorized	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------