



VM91214CU

Dual Row HI Conf 12+14 Way 100A Switch 2*100A RCCB

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Dimensions

Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	364 mm

Cover, door

Interlockable	No
---------------	----

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

Equipment

Number of rows	2
Can be accessorized	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------