



VM91214CUK

**Dual Row HI Conf 12+14 Way 100A Switch 2\*100A RCCB with Knockouts**

**Technical characteristics**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50 Hz

**Dimensions**

Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	364 mm

**Cover, door**

Type of door closing	non keylock
Interlockable	No

**Materials**

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white

**Equipment**

Number of rows	2
Can be accessorized	Yes