



VM912CU

12 Way HI Cf 100A Switch 2*100A 30mA RCCB

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Dimensions

Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	400 mm

Cover, door

Type of door closing	non keylock
Interlockable	No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white

Equipment

Number of rows	1
Can be accessorized	Yes