



VM912CUK

## 12 Way HI Cf 100A Switch 2\*100A 30mA RCCB with Knockouts

### Technical characteristics

#### Architecture

Fixing mode	surface-mounting
-------------	------------------

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

#### Dimensions

Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	400 mm

#### Cover, door

Type of door closing	non keylock
Interlockable	No

#### Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white

#### Equipment

Number of rows	1
Can be accessorized	Yes