



VM91620CUSPD

**Design 30, Dual Row, 15+20 Way HI 100A Sw 2\*100A 30mA RCCB Type A SPD**

**Technical characteristics**

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50 Hz

**Dimensions**

Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	472 mm

**Cover, door**

Type of door closing	non keylock
Interlockable	No

**Materials**

Colour	pure white
Colour	white

**Equipment**

Number of rows	2
Can be accessorized	Yes

**Standards**

European directive WEEE	concerned
-------------------------	-----------