



VM91820HK

Dual Row 18+20W 100A Switch 2*100A 30mA RCCB with Knockouts

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Dimensions

Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	471 mm

Cover, door

Type of door closing	non keylock
Interlockable	No

Materials

Colour	pure white
Colour	white

Equipment

Number of rows	2
Can be accessorized	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------