



VM918C

Consumer unit, Design 30, 18way, twin tariff, config, 2*100A sw

Technical characteristics

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
Overvoltage protection	Yes

Capacity

Number of modules	18
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	102.50 mm
Height	240 mm
Width	471 mm
Thickness of sidewall	1 mm

Cover, door

Interlockable	Yes
Door/cover is transparent	No

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	2
Number of RCCB in enclosure	2

Equipment

Number of rows	1
----------------	---

Number of rails	1
Extension possible	No
Safety	
Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC