



VM946H

Dual Row 4+6 Way 100A Switch 2*100A 30mA RCCB

Technical Characteristics

Fixing mode	surface-mounting
Rated operational voltage Ue	230 V
Frequency	50 Hz
Rated current	100 A
Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	220 mm
Number of modules	10
Type of door closing	non keylock
Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Number of rows	2
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC