



VM946HK

Dual Row 4+6 Way 100A Switch 2*100A 30mA RCCB with Knockouts

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Dimensions

Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	220 mm

Cover, door

Interlockable	No
---------------	----

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

Equipment

Number of rows	2
Can be accessorized	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------