



VM955H

Metal Consumer Unit 10 Way Split Load 5+5 100A Switch 2*100A 30mA RCCB

Technical characteristics

Architecture

| | |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 230 V |
| Frequency | 50 Hz |

Dimensions

| | |
|-----------------------------|----------|
| Depth of installed product | 102.5 mm |
| Height of installed product | 240 mm |
| Width of installed product | 364 mm |

Cover, door

| | |
|---------------|----|
| Interlockable | No |
|---------------|----|

Materials

| | |
|------------|-----------------------|
| Colour | pure white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | Steel |

Equipment

| | |
|---------------------|-----|
| Number of rows | 1 |
| Can be accessorized | Yes |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|