



VM955H

**Metal Consumer Unit 10 Way Split Load 5+5 100A Switch 2\*100A 30mA  
RCCB**

**Technical Characteristics**

Fixing mode	surface-mounting
Rated operational voltage Ue	230 V
Frequency	50 Hz
Rated current	100 A
Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	364 mm
Number of modules	10
Type of door closing	non keylock
Interlockable	No
Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Number of rows	1
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC