



VM966TG

12 Way 100A 100mA Time Delay + 2 x 100A RCCB

Technical Characteristics

Fixing mode	surface-mounting
With remote signalling contact	No
Depth of installed product	102 mm
Height of installed product	240 mm
Width of installed product	400 mm
Number of modules	12
RAL colour number	9010
Number of rows	1
Can be accessorized	Yes
Protection index IP	IP2XC