



VMA90405H

Dual Row 100A Sw, 2*100A 30mA RCCB, 4+5 Way, 2 pole busbar, ARC Fault

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Frequency 50 Hz

Dimensions

Depth of installed product 102.5 mm

Height of installed product 480 mm

Width of installed product 293 mm

Cover, door

Type of door closing non keylock

Interlockable No

Materials

Colour white

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Equipment

Number of rows 2

Can be accessorized Yes

Standards

European directive WEEE concerned

Safety

Protection index IP IP2XC

Protection class isol.class II