



VMA90507HKSPD

Dual Row 100A Sw, 2*100A 30mA RCCB, 5+7 Way, 2 pole busbar, ARC Fault + SPD KO

Technical Characteristics

| | |
|-----------------------------|-----------------------|
| Fixing mode | surface-mounting |
| Frequency | 50 Hz |
| Rated current | 100 A |
| Depth of installed product | 102.5 mm |
| Height of installed product | 480 mm |
| Width of installed product | 364 mm |
| Number of modules | 12 |
| Type of door closing | non keylock |
| Interlockable | No |
| Colour | white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| RAL colour number | 9010 |
| Material | Steel |
| Number of rows | 2 |
| Can be accessorized | Yes |
| European directive WEEE | concerned |
| Protection index IP | IP2XC |
| Protection class | isol.class II |
