



VMA90607HK

Dual Row 100A Sw, 2*100A 30mA RCCB, 6+7 Way, 2 pole busbar, ARC Fault KO

Technical characteristics

Main electrical features

Frequency	50 Hz
-----------	-------

Dimensions

Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	364 mm

Cover, door

Type of door closing	non keylock
Interlockable	No

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white

Equipment

Number of rows	2
Can be accessorized	Yes

Safety

Protection class	isol.class II
------------------	---------------