



VMA90810HKSPD

Dual Row 100A Sw, 2*100A 30mA RCCB,8+10 Way, 2 pole busbar,ARC Fault + SPD KO

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Frequency	50 Hz
-----------	-------

Dimensions

Depth of installed product	102.5 mm
----------------------------	----------

Height of installed product	480 mm
-----------------------------	--------

Width of installed product	472 mm
----------------------------	--------

Cover, door

Interlockable	No
---------------	----

Materials

Colour	white
--------	-------

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	Steel
----------	-------

Equipment

Number of rows	2
----------------	---

Can be accessorized	Yes
---------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	isol.class II
------------------	---------------