



VMA90910HK

**Dual Row 100A Sw, 2\*100A 30mA RCCB, 9+10 Way, 2 pole busbar, ARC Fault KO**

**Technical characteristics**

**Architecture**

Fixing mode surface-mounting

**Main electrical features**

Frequency 50 Hz

**Dimensions**

Depth of installed product 102.5 mm

Height of installed product 480 mm

Width of installed product 472 mm

**Cover, door**

Type of door closing non keylock

Interlockable No

**Materials**

Colour white

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

**Equipment**

Number of rows 2

Can be accessorized Yes

**Standards**

European directive WEEE concerned

**Safety**

Protection index IP IP2XC

Protection class isol.class II