



VML112SPDRK

**Design 10 Consumer Unit 12 Way 100A Sw Disconnect Incomer Round KO + T2 SPD**

**Technical characteristics**

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	No

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
Overvoltage protection	No

**Capacity**

Number of modules	12
-------------------	----

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Depth	100 mm
Height	98.20 mm
Width	368.40 mm
Number of width units	12
Thickness of sidewall	1 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	9010
Colour	Pure white
Material	Steel

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of RCCB in enclosure	0
-----------------------------	---

**Equipment**

Number of rows	1
----------------	---

Number of rails	1
Extension possible	No
<b>Safety</b>	
Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC