

VML118SPD

**Design 10, 18 way 100A SW SPD**

**Technical characteristics**

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	No

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
Overvoltage protection	No

**Capacity**

Number of modules	38
-------------------	----

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Depth	100 mm
Height	246 mm
Width	478 mm
Thickness of sidewall	1 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	9010
Colour	Pure white
Material	Steel

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of RCCB in enclosure	2
-----------------------------	---

**Equipment**

Number of rows	1
Number of rails	1

Extension possible

No

**Safety**

---

Impact resistance IK

IK05

---

Ingress Protection (IP) class

IP2XC