



VML60610CUSPD

Design 10, Dual Row, 6+10 Way HI 63A Sw 2*63A 30mA RCCB Type A SPD

Technical Characteristics

Fixing mode	surface-mounting
With remote signalling contact	No
Depth of installed product	100 mm
Height of installed product	486 mm
Width of installed product	299 mm
RAL colour number	9010
Number of rows	2
Can be accessorized	Yes
Protection index IP	IP2XC