



VML610CUSPD

Design 10 , 10 way Configureable HI 63A Sw 2*63A 30mA RCCB Type A SPD

Technical Characteristics

Fixing mode	surface-mounting
Rated current	63 A
Depth of installed product	100 mm
Height of installed product	246 mm
Width of installed product	406 mm
Interlockable	No
Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Number of rows	1
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC