



VML633H

6 Way 3+3 63A Switch 2*63A 30mA Type A RCCB

Technical Characteristics

Fixing mode	surface-mounting
Rated current	63 A
Depth of installed product	100 mm
Height of installed product	246 mm
Width of installed product	296.8 mm
Interlockable	No
Material	Steel
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC
