



VML666H

12 Way 6+6 63A Switch 2*63A 30mA Type A RCCB

Technical Characteristics

Fixing mode	surface-mounting
Rated current	63 A
Depth of installed product	100 mm
Height of installed product	246 mm
Width of installed product	406 mm
Number of modules	12
Interlockable	No
Material	Steel
Number of rows	1
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC