



VML666RK

12 Way 6+6 63A Switch 2*63A 30mA Type A RKO

Technical Characteristics

| | |
|-----------------------------|------------------|
| Fixing mode | surface-mounting |
| Rated current | 63 A |
| Depth of installed product | 100 mm |
| Height of installed product | 246 mm |
| Width of installed product | 406 mm |
| Number of modules | 12 |
| Interlockable | No |
| Material | Steel |
| Number of rows | 1 |
| Can be accessorized | Yes |
| European directive WEEE | concerned |
| Protection index IP | IP2XC |