



VML90610CUSPD

**Design 10, Dual Row, 6+10 Way HI 100A Sw 2\*100A 30mA RCCB Type A SPD**

**Technical characteristics**

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	No

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
Overvoltage protection	Yes

**Capacity**

Number of modules	16
-------------------	----

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Depth	100 mm
Height	486 mm
Width	299 mm
Thickness of sidewall	0.90 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	9010
Colour	Pure white
Material	Steel

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of RCCB in enclosure	2
-----------------------------	---

**Equipment**

Number of rows	2
Number of rails	2

Extension possible	No
--------------------	----

**Safety**

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC