



VML908CUSPD

**Design 10 , 8 way Configurable HI 100A Sw 2\*100A 30mA RCCB Type A SPD**

**Technical characteristics**

**Installation, mounting**

|                            |                  |
|----------------------------|------------------|
| Mounting on                | Surface mounting |
| Suitable for outdoor usage | No               |

**Architecture**

|                 |   |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

**Functions**

|                            |     |
|----------------------------|-----|
| Has protection main switch | Yes |
| Overvoltage protection     | Yes |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 8 |
|-------------------|---|

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

**Dimensions**

|                       |         |
|-----------------------|---------|
| Depth                 | 100 mm  |
| Height                | 246 mm  |
| Width                 | 370 mm  |
| Thickness of sidewall | 0.90 mm |

**Cover, door**

|                           |    |
|---------------------------|----|
| Interlockable             | No |
| Door/cover is transparent | No |

**Materials**

|          |            |
|----------|------------|
| RAL code | 9010       |
| Colour   | Pure white |
| Material | Steel      |

**Connection**

|                             |   |
|-----------------------------|---|
| Number of accessible phases | 1 |
|-----------------------------|---|

**Scope of delivery**

|                             |   |
|-----------------------------|---|
| Number of RCCB in enclosure | 2 |
|-----------------------------|---|

**Equipment**

|                 |   |
|-----------------|---|
| Number of rows  | 1 |
| Number of rails | 1 |

Extension possible

No

**Safety**

---

Impact resistance IK

IK05

---

Ingress Protection (IP) class

IP2XC