



VML91014CUSPD

**Dual Row,10+14 Way Hi Integrity 100A Switch 2*100A 30mA Type RCCB
Type 2 SPD**

Technical Characteristics

Fixing mode	surface-mounting
Rated current	100 A
Depth of installed product	100 mm
Height of installed product	486 mm
Width of installed product	370 mm
Interlockable	No
Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Number of rows	2
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC