



VML914CUSPDRK

14 Way Hi Integrity 100A Switch 2*100A 30mA RCCB Type 2 SPD RKO

Technical Characteristics

Fixing mode	surface-mounting
Rated current	100 A
Depth of installed product	100 mm
Height of installed product	246 mm
Width of installed product	478 mm
Interlockable	No
Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Number of rows	1
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC