



VML966RK

12 Way 6+6 100A Switch 2*100A 30mA RCCB Type A Round KO

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Dimensions

Depth of installed product	100 mm
Height of installed product	245 mm
Width of installed product	404.2 mm

Cover, door

Interlockable	No
---------------	----

Materials

Material	Steel
----------	-------

Equipment

Number of rows	1
Can be accessorized	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------