



VMLA90607H

**Dual Row 100A Sw, 2\*100A 30mA RCCB, 6+7 Way, 2 pole busbar, ARC Fault**

**Technical characteristics**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Main electrical features**

Frequency	50 Hz
-----------	-------

**Dimensions**

Depth of installed product	100 mm
Height of installed product	486 mm
Width of installed product	370 mm

**Cover, door**

Type of door closing	non keylock
Interlockable	No

**Materials**

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white

**Equipment**

Number of rows	2
Can be accessorized	Yes

**Safety**

Protection class	isol.class II
------------------	---------------