



VMLF112SPD

## 12 way 100A Switch Type 2 SPD

### Technical characteristics

#### Installation, mounting

Mounting on	Flush mounting
Suitable for outdoor usage	No

#### Architecture

Number of poles	2
-----------------	---

#### Functions

Overvoltage protection	Yes
------------------------	-----

#### Capacity

Number of modules	12
-------------------	----

#### Electric current

Rated current	100 A
---------------	-------

#### Dimensions

Depth	104 mm
Height	282 mm
Width	407 mm
Thickness of sidewall	1 mm

#### Cover, door

Interlockable	No
Door/cover is transparent	No

#### Materials

RAL code	9010
Colour	Pure white
Material	Steel

#### Connection

Number of accessible phases	1
-----------------------------	---

#### Equipment

Number of rows	1
Number of rails	1
Extension possible	No

#### Safety

Impact resistance IK	IK05
----------------------	------

