



VMLF114

**Consumer unit, Design 10, flush mounted, 14 way, 100A, switch disconnecter incomer**

#### Technical characteristics

##### Installation, mounting

Mounting on	Flush mounting
Suitable for outdoor usage	No

##### Architecture

Number of poles	2
-----------------	---

##### Functions

Has protection main switch	Yes
Overvoltage protection	No

##### Capacity

Number of modules	14
-------------------	----

##### Electric current

Rated current	100 A
---------------	-------

##### Dimensions

Depth	104 mm
Height	282 mm
Width	407 mm
Thickness of sidewall	1 mm

##### Cover, door

Interlockable	No
Door/cover is transparent	No

##### Materials

RAL code	9010
Colour	Pure white
Material	Steel

##### Connection

Number of accessible phases	1
-----------------------------	---

##### Scope of delivery

Number of RCCB in enclosure	0
-----------------------------	---

##### Equipment

Number of rows	1
Number of rails	1

Extension possible	No
--------------------	----

**Safety**

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC