



VMLF912C

## 12 Way Flush 100A Switch 2\*100A 30mA RCCB

### Technical characteristics

#### Installation, mounting

Mounting on	Flush mounting
Suitable for outdoor usage	No

#### Architecture

Number of poles	2
-----------------	---

#### Functions

Has protection main switch	Yes
Overvoltage protection	Yes

#### Capacity

Number of modules	12
-------------------	----

#### Electric current

Rated current	100 A
---------------	-------

#### Dimensions

Depth	104 mm
Height	282 mm
Width	443 mm
Thickness of sidewall	1 mm

#### Cover, door

Interlockable	No
Door/cover is transparent	No

#### Materials

RAL code	9010
Colour	Pure white
Material	Steel

#### Connection

Number of accessible phases	1
-----------------------------	---

#### Scope of delivery

Number of RCCB in enclosure	2
-----------------------------	---

#### Equipment

Number of rows	1
Number of rails	1

Extension possible	No
<b>Safety</b>	
Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC