



VR640EVSPD

6 Way 100A Switch disconnecter with 40A DP Switch Neutral RCBO+Type 2 Surge Prot

Technical characteristics

Installation, mounting

Mounting on	Base
Suitable for outdoor usage	No

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
Overvoltage protection	No

Configuration

Number of arc fault detection devices AFDD	0
--	---

Capacity

Number of modules	6
-------------------	---

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	83 mm
Height	206 mm
Width	145 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	White
Material	Metal

Connection

Number of accessible phases	2
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	0
Number of RCCB in enclosure	1

Equipment	
Number of groups	0
Number of light groups	0
Number of rows	1
With energy meter	No
Number of rails	0
Extension possible	No
With bell transformer	No
Safety	
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Protection class	Isolation class III