



## 6 Way 100A Switch disconnector with 40A DP Switch Neutral RCBO+Type 2 Surge Prot

## **Technical characteristics**

Installation, mounting	
Mounting on	Base
Suitable for outdoor usage	No
Architecture	
Number of poles	2
Functions	
Has protection main switch	Yes
Overvoltage protection	No
Configuration	
Number of arc fault detection devices AFDD	0
Capacity	
Number of modules	6
Electric current	
Rated current	100 A
Dimensions	
Depth	83 mm
Height	206 mm
Width	145 mm
Cover, door	
Interlockable	No
Door/cover is transparent	No
Materials	
RAL code	9010
Colour	White
Material	Metal
Connection	
Number of accessible phases	2
Scope of delivery	
Number of earth leakage circuit breaker type A	0
Number of RCCB in enclosure	1
	-

Equipment	
Number of groups	0
Number of light groups	0
Number of rows	1
With energy meter	No
Number of rails	0
Extension possible	No
With bell transformer	No
Safety	
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Protection class	Isolation class III